


THM WO VIN 25.4/19 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 2 - 4 mm, 25.4 x 19 mm, white
Order No.	2657120000
Type	THM WO VIN 25.4/19 WS
GTIN (EAN)	4050118675252
Qty.	2,000 pc(s).
compatible printer	2599430000 2599440000

THM WO VIN 25.4/19 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.07 mm	Depth (inches)	0.003 inch
Height	25.4 mm	Height (inches)	1 inch
Width	19 mm	Width (inches)	0.748 inch
Net weight	0.13 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Adhesive	Polyacrylate adhesive	
Approval acc. to UL 969	No	
Colour	white	
Halogen	Yes	
Material	Vinyl film	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Label reel
Number per roll	2,000	
Operating temperature range	-40...80 °C	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Printed characters	without	
Printing method	Thermal transfer	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Version	Self-adhesive	
Width	19 mm	

Conductor and cable markers

Conductor O.D.	2 - 4 mm	Conductor O.D., max.	4 mm
Conductor O.D., min.	2 mm	Conductor cross-section, max.	12 mm ²
Cross-section for connected wire	12 mm ²	Halogen	Yes
Wire connection cross section AWG, max.	AWG 14	Wire connection cross section AWG, min.	AWG 18

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

THM WO VIN 25.4/19 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

Drawings

