

IE-FPOD2UG0010MSDESDEX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.

The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5 , 6 and 14
- consistently Cat. 6_A with **STEADYTEC®** technology
- in IP20 and IP67
- all relevant industrial connections: RJ45, SC, ...
- comprehensive range of accessories

General ordering data

Version	Dragline cable, SC IP 67 PushPull V14 metal, SC IP 67 PushPull V14 metal, 980 µm, 10 m
Order No.	2703680100
Type	IE-FPOD2UG0010MSDESDEX
GTIN (EAN)	4050118716238
Qty.	1 pc(s).

IE-FPOD2UG0010MSDESDEX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	10 m	Length (inches)	393.701 inch
Net weight	447 g		

Fibre-optic

Attenuation	≤ 160 dB/km at 650 nm	Bandwidth	> 35 MHz*100 m at 650 nm
Fibre type	POF		

Cable structure

Core diameter	980 µm	Primary coating	245 µm
---------------	--------	-----------------	--------

Classifications

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03
ECLASS 13.0	27-06-10-03	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--