

HDC 10B TSS 1M32 WMP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Our flange-mounted housings made of plastic have a built-in cable gland and a screw interlock. They seal directly onto the panel wall and can therefore be used without an attachment housing. The housings are impressive with their low weight and optimal protection against contamination, water and vibrations.

General ordering data

Version	HDC enclosures, Size: 4, Protection degree: IP66 (in plugged condition), IP67 (in plugged condition), Cable entry from side, Screw, , Size of cable entries: M 32
Order No.	2716760000
Type	HDC 10B TSS 1M32 WMP
GTIN (EAN)	4050118803631
Qty.	1 pc(s).

HDC 10B TSS 1M32 WMP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	97 mm	Height (inches)	3.819 inch
Net weight	149 g		

Temperatures

Ambient temperature	-40 °C... 100 °C
---------------------	------------------

Cable Gland WMP

Cable diameter, min.	11 mm	Cable diameter, max.	21 mm
AF size	30 mm	Size of cable entries	M 32

Dimensions

Cable entry	w. cable glands	Height of housing B	97 mm
-------------	-----------------	---------------------	-------

General data

EMC housings	No	Housing main material	PA
Material of locking element		Protection degree	IP66 (in plugged condition), IP67 (in plugged condition)
	Stainless steel, rust-proof		
Tightening torque	3 Nm	UL 94 flammability rating	V-0

Version

BG	4	Cable entry	w. cable glands
Colour (RAL)	RAL 9011	Design of housing	Cable entry from side
Design of locking system	Screw	Number of cable entry sideways	1
Number of cable glands	1	Sealing	NBR
Size	4	Size of cable entries	M 32
Suitable for ModuPlug®	Yes	Tightening torque	3 Nm
Top part/bottom part/lid	upper part		

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02
ECLASS 13.0	27-44-02-02	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

HDC 10B TSS 1M32 WMP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223801

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's declaration
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

HDC 10B TSS 1M32 WMP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings**