


VT SF 4.5/21 MC NE GN V0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Version	SlimFix, Conductor and cable markers, 21 x 7.4 mm, green
Order No.	2741190000
Type	VT SF 4.5/21 MC NE GN V0
GTIN (EAN)	4050118843736
Qty.	192 pc(s).

VT SF 4.5/21 MC NE GN V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	6.5 mm	Depth (inches)	0.256 inch
Height	21 mm	Height (inches)	0.827 inch
Width	7.4 mm	Width (inches)	0.291 inch
Net weight	0.812 g		

General data

Colour	green	Halogen	No
Material	Polyamide 66	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Type of printing	neutral
UL 94 flammability rating	V-0	Width	7.4 mm

Conductor and cable markers

Conductor O.D., max.	4.9 mm	Conductor O.D., min.	4.1 mm
Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	4 mm ²
Cross-section for connected wire	4 - 6 mm ²	Halogen	No

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

VT SF 4.5/21 MC NE GN V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

