

SU 10.16 BFSC S 35X12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

General ordering data

Version	PCB plug-in connector, Mounting screw
Order No.	2812290000
Type	SU 10.16 BFSC S 35X12
GTIN (EAN)	4064675294955
Qty.	50 pc(s).
Product data	

SU 10.16 BFSC S 35X12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	0.3 g
------------	-------

Material data

Contact material	Cu-alloy	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C		

Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984
-------------------------	------------------------

Packing

VPE length	60 mm	VPE width	60 mm
VPE height	25 mm		

Classifications

ETIM 6.0	EC000887	ETIM 7.0	EC000887
ETIM 8.0	EC003861	ETIM 9.0	EC003861
ETIM 10.0	EC003861	ECLASS 9.0	23-11-01-90
ECLASS 9.1	23-11-01-90	ECLASS 10.0	23-11-01-90
ECLASS 11.0	23-11-01-90	ECLASS 12.0	23-11-01-90
ECLASS 13.0	23-11-01-90	ECLASS 14.0	23-11-01-90
ECLASS 15.0	23-11-01-90		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Important note

IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.
Notes	Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Downloads

Engineering Data	CAD data – STEP
------------------	---------------------------------