

IE-TO-RJ45-C-ZP-C5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Mounting rail outlet, RJ45 junction design according to
IEC 60603-7-51

General ordering data

Version	Mounting rail outlet, RJ45, IP20, Cat. 5
Order No.	2819260000
Type	IE-TO-RJ45-C-ZP-C5
GTIN (EAN)	4064675330110
Qty.	10 pc(s).

IE-TO-RJ45-C-ZP-C5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	15 g
------------	------

Temperatures

Operating temperature	-40 °C...80 °C
-----------------------	----------------

General data

Connection 1	RJ45	Connection 2	RJ45
Wiring	Coupling	Colour	beige, black
Housing main material	Plastic, PA 66 UL V0 E63957	Category	Cat. 5
Contact surface	Gold over nickel	Type of mounting	TS 35
Shielding	unshielded	Protection degree	IP20
Plugging cycles	750 (RJ45)		

Electrical properties

Current-carrying capacity at 50 °C	1 A	Dielectric strength, contact / contact	≥ 1000 V AC/DC
Dielectric strength, contact / shield	≥ 1500 V AC/DC	Rated voltage	50 V

General standards

Connector standard	IEC 60603-7-51
--------------------	----------------

Classifications

ETIM 6.0	EC000313	ETIM 7.0	EC000313
ETIM 8.0	EC000313	ETIM 9.0	EC000313
ETIM 10.0	EC000313	ECLASS 9.0	27-44-03-20
ECLASS 9.1	19-17-01-25	ECLASS 10.0	27-44-03-20
ECLASS 11.0	27-44-03-20	ECLASS 12.0	27-44-03-20
ECLASS 13.0	27-44-03-20	ECLASS 14.0	27-44-03-20
ECLASS 15.0	27-44-03-20		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

IE-TO-RJ45-C-ZP-C5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

