

WIL-AXXXX-FXSF-5700-X800-GST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Order No.	2979350000
Type	WIL-AXXXX-FXSF-5700-X800-GST
GTIN (EAN)	4099986832794
Qty.	1 pc(s).

WIL-AXXXX-FXSF-5700-X800-GST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	135 mm	Depth (inches)	5.315 inch
Height	38 mm	Height (inches)	1.496 inch
Width	816 mm	Width (inches)	32.126 inch
Net weight	300 g		

Temperatures

Operating temperature	-20 - 45°C
-----------------------	------------

Cable technical specifications

Housing main material	hard anodised aluminium
-----------------------	-------------------------

Connection data

Number of poles	3
-----------------	---

Electric data

Rated voltage	230 V AC	Power	32.5 W
Dimmable	yes, stepless dimming		

General technical data

Light colour (CCT)	5700K, White	Light current	5,825 lm
Emitting angle	100 °	Operating life	60.000 h
Type of mounting	Screw mounting	Protection degree	IP40

Material data

Housing main material	hard anodised aluminium
-----------------------	-------------------------

Classifications

ETIM 6.0	EC000996	ETIM 7.0	EC000996
ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 9.1	27-11-06-35
ECLASS 10.0	27-11-06-35	ECLASS 11.0	27-11-06-35
ECLASS 12.0	27-11-06-35	ECLASS 13.0	27-11-06-35
ECLASS 14.0	27-11-06-35	ECLASS 15.0	27-11-06-35

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	60b0f8b3-d5d4-4f2d-a3c8-d2f055e5e550

WIL-AXXXX-FXSF-5700-X800-GST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)