

PAC-UNIV-HE20-LCF-1M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

General ordering data

Version	Pre-assembled cable, PAC, Cable LiYY, 0.14 mm²
Order No.	7789388010
Type	PAC-UNIV-HE20-LCF-1M
GTIN (EAN)	4032248916078
Qty.	1 pc(s).

PAC-UNIV-HE20-LCF-1M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	60.87 g
------------	---------

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
---------------------	-------------	-----------------------	-------------

General Data

Cable	Cable LiYY	Cable length	1 m
Connector PLC side	H0.25/10 (FERRULES 0.25mm ²)	Interface connector	FLAT CABLE CONECTOR HE10 20P
Material	PVC	Number of poles, min.	20-pole
Outer diameter	8.6 ± 1 mm	Suitable for	Digital signals
Wire cross-section	0.14 mm ²		

Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
High voltage test	1 KV/1s	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 Vdc ≤ 25 Vac	Resistance	≤ 150 mΩ/m
Total current, max.	3 A		

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20
ECLASS 13.0	27-24-22-20	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Colours chart
Catalogues	Catalogues in PDF-format