

KTB GP 40XX15V CD S4 PE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Integrate, expand and customise: The ideal expansion for every application**

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembled

General ordering data

Order No.	8000114909
Type	KTB GP 40XX15V CD S4 PE
GTIN (EAN)	4099986797499
Qty.	1 pc(s).

KTB GP 40XX15V CD S4 PE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	3 mm	Depth (inches)	0.118 inch
Height	354 mm	Height (inches)	13.937 inch
Width	117 mm	Width (inches)	4.606 inch
Net weight	997.4 g		

General information

Areas of use	Process industry	Flange plate	Yes
Gland plates	left, right	Installation advice	Screw mounting
Integral fixing	Screwed	Material	Stainless steel 1.4404 (316L)
Material thickness	3 mm	Protection class (UL)	Type 3, Type 4X, Type 12
Surface finish	electropolished		

General information on accessories

Material	Stainless steel 1.4404 (316L)	Material thickness	3 mm
Surface finish	electropolished		

Housing earth

Flange plate earthing	Welded-on M6 x 10 stainless-steel earth stud
-----------------------	--

Classifications

ETIM 6.0	EC000211	ETIM 7.0	EC000211
ETIM 8.0	EC000211	ETIM 9.0	EC000211
ETIM 10.0	EC000211	ECLASS 9.0	27-14-24-21
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-14-24-21
ECLASS 11.0	27-14-24-21	ECLASS 12.0	27-14-24-21
ECLASS 13.0	27-14-24-21	ECLASS 14.0	27-14-24-21
ECLASS 15.0	27-14-24-21		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/
ROHS	Conform

Downloads

Catalogues	Catalogues in PDF-format
------------	--