

CTX CM 1.6/2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for turned contacts**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.14mm², 4mm², W crimp
Order No.	9018490000
Type	CTX CM 1.6/2.5
GTIN (EAN)	4008190884598
Qty.	1 pc(s).
Replacement parts	1121010000

CTX CM 1.6/2.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Net weight	679.78 g		

Technical data

Description of article	Crimping tool for HD, HE and ConCept M10/M5 contacts, 0.14-4 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Conductor cross-section, max. AWG	AWG 12	Conductor cross-section, min. AWG	AWG 26
Crimping range, max.	4 mm ²	Crimping range, min.	0.14 mm ²
Type of contact	Turned contacts		

tool data crimping

Crimping profile 5	4 mm ²	Crimping type/profile	W crimp
Wire end ferrules cross-section, max.	4 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11
ECLASS 13.0	21-04-38-11	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Downloads

Engineering Data	CAD data – STEP
User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

CTX CM 1.6/2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

