

MEKA BR CST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For coaxial cable and round (shielded) data cables from 2.5 to 8mm diameter
- 1-, 2- and 3-level stripping in one operation

General ordering data

Version	Accessories, Cutter cassette
Order No.	9032010000
Type	MEKA BR CST
GTIN (EAN)	4008190135928
Qty.	1 pc(s).

MEKA BR CST

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	20 mm	Depth (inches)	0.787 inch
Height	10 mm	Height (inches)	0.394 inch
Width	30 mm	Width (inches)	1.181 inch
Net weight	0.22 g		

Technical data

Description of article	Cutter cassette for CST, 3-part, length 7.5mm, 3.5mm
------------------------	--

Stripping tools

Colour	brown	Stripping size B	7.5 mm
Stripping size C	3.5 mm		

Classifications

ETIM 6.0	EC001509	ETIM 7.0	EC001509
ETIM 8.0	EC001509	ETIM 9.0	EC001509
ETIM 10.0	EC001509	ECLASS 9.0	21-04-92-37
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-92-37
ECLASS 11.0	21-04-48-91	ECLASS 12.0	21-04-48-91
ECLASS 13.0	21-04-48-91	ECLASS 14.0	21-04-48-91
ECLASS 15.0	21-04-48-91		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

Catalogues	Catalogues in PDF-format
------------	--