

STRIPPER COAX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

Version	Sheathing strippers
Order No.	9918030000
Type	STRIPPER COAX
GTIN (EAN)	4032248359141
Qty.	1 pc(s).

STRIPPER COAX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	18.5 mm	Depth (inches)	0.728 inch
Height	20.5 mm	Height (inches)	0.807 inch
Width	97 mm	Width (inches)	3.819 inch
Net weight	39 g		

Technical data

Description of article	Cable sheathing stripper for coaxial and PVC round cables
------------------------	---

Stripping tools

Cable type	Coaxial data and round cables	Conductor cross-section, max.	44 mm ²
Conductor cross-section, min.	18 mm ²	Max. conductor diameter	7.5 mm
Min. conductor diameter	4.8 mm	Workable cable	PVC cables

Classifications

ETIM 6.0	EC000163	ETIM 7.0	EC000163
ETIM 8.0	EC000163	ETIM 9.0	EC000163
ETIM 10.0	EC000163	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90
ECLASS 13.0	21-04-90-90	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

STRIPPER COAX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

