



Representative Image

Catalog No. 3120-30**Description: 2 INCH AROMRED CABLE CONN****UPC No 786210947709****Home > Cable Protection Systems > T&B Cord & Cable Fittings > Flex connectors**

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 2 Inch, Knockout Size 2 Inch, Cable Range 2.312 to 2.500 Inch, Malleable Iron with Zinc Plating, Nylon Insulated

Descriptors

Category	Flex connectors
Special Features	The Tough Lining of Insulation and The Tite-Bite Principles Make These Connectors a Must When Conductors are Subject to Conditions of Vibration or Strain.
Application	For Use with Armored Cable and Flexible Metal Conduit.

Specifications

Conductor Range	2.312 to 2.500 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

Classifications

Brand Name	T&B Cord & Cable Fittings
Standard	UL E23018

Dimensions

Size	2 Inch
------	--------

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other