

SBBSM4040-1 *Proto Advantage*

Datasheet revision 1.1

www.Proto-Advantage.com

Large Surface mount breadboard 1600 SMT pads

Product Highlights

Immersion Gold Finish
Single Sided
1600 pads in total
0.1" pad grid
40 rows, 40 columns

Specifications

Dimensions:	4.1" x 4.2" x 0.0625"
PCB construction:	FR-4 UL94V-0
PCB operating temperature range:	-40°C to +130°C
PCB reflow maximum temperature:	+260°C
Pad size:	Square: 2.0mm x 2.0mm (0.079" x 0.079")

