

GM-270

27" Open Frame Gaming Monitor with Touchscreen



Features

- 27" 16:9 LCD panel with LED backlight with 40,000-hour service life
- 10-point PCAP touchscreen
- Anti-fingerprint surface treatment for ease of cleaning and enhanced readability
- Wide viewing angles support for both portrait and landscape modes

Ordering Information

- GM-270
27" Open Frame Gaming Monitor with Touchscreen

Optional Accessories

- AC Adapter

GM-270			
Display		Environmental	
Size	27"	Operating Temperature	0°C to 50°C
Resolution	1920 x 1080	Storage Temperature	-20°C to 60°C
Aspect Ratio	16:9	Humidity	10% to 80% @ 40°C (non-condensing)
Color	16.7M	Surface Hardness	7H
Brightness (Nits)	240 nits	Vibration	Operating: 1G random 5 to 500Hz
Backlight Life (Hrs)	40,000	Shock	Operating: 20G acceleration part to part, 11ms
Viewing Angle (U/D/R/L)	89/89/89/89	Certifications & Compliance	CE/FCC
Contrast Ratio	3000:1	Power Input	DC-12V 5A Max.
Touchscreen	10-point, PCAP, Anti-fingerprint coating	Power Consumption	Max. 25W
Bonding	Air bonding	Mechanical	
I/O		Weight	8 kg
USB Port	USB type B (for touch)	Dimensions (H x W x D)	641 x 380 x 58 mm
Video	DPx1, DVIx1, VGAx1	Mounting	VESA Mount, M4 MIS-D 75mm x 75mm, 100mm x 100mm (Standard)
Audio	w/o Audio		