

GM-320SG

32" LED-framed
Gaming Monitor



Features

- 32" 16:9 LCD panel with LED backlight with 30,000-hour service life
- Display with surrounding LED (addressable RGB LEDs)
- Anti-fingerprint surface treatment for ease of cleaning and enhanced readability
- Wide viewing angles support for both portrait and landscape modes

Ordering Information

- GM-320SG
32" LED-framed Gaming Monitor

Optional Accessories

- AC Adapter
- LED Control Board

GM-320SG			
Display		Environmental	
Size	32"	Operating Temperature	0°C to 50°C
Resolution	1920 x 1080	Storage Temperature	-20°C to 60°C
Aspect Ratio	16:9	Humidity	10% to 80% @40°C (non-condensing)
Color	16.7M	Surface Hardness	6H
Brightness (nits)	270 nits	Vibration	Operating: 1G random 10 to 300Hz
Backlight Life (h)	30,000	Shock	Operating: 20G acceleration part to part, 11ms
Viewing Angle (U/D/R/L)	89/89/89/89	Certification & Compliance	CE/FCC
Contrast Ratio	1200:1	Power Input	DC-24V 2.5A Max.
Surface Treatment	Anti-finger coating	Power Consumption	Max. 60W
Bonding	Air bonding	LED Strip Power	5V DC, 2.4A Max.
I/O		Mechanical	
Video	DPx1, DVIx1, VGAx1	Weight	12.2 kg
Audio	w/o Audio	Dimension (H x W x D)	759.4 x 451.9 x 52 mm
		Mounting	VESA Mount, M6 200mm x 200mm (Standard)