

# GM-320

## 32" Open Frame Gaming Monitor with Touchscreen



### Features

- 32" 16:9 LCD panel with LED backlight with 30,000-hour service life
- 10-point PCAP touchscreen
- Anti-fingerprint surface treatment for ease of cleaning and enhanced readability
- Wide viewing angles support for both portrait and landscape modes

### Ordering Information

- GM-320  
32" Open Frame Gaming Monitor with Touchscreen

### Optional Accessories

- AC Adapter

GM-320			
<b>Display</b>		<b>Environmental</b>	
Size	32"	Operating Temperature	0°C to 50°C
Resolution	1920 x 1080	Storage Temperature	-20°C to 60°C
Aspect Ratio	16:9	Humidity	10% to 80% @ 40°C (non-condensing)
Color	16.7M	Surface Hardness	6H
Brightness (Nits)	250 nits	Vibration	Operating: 1G random 10 to 300Hz
Backlight Life (Hrs)	30,000	Shock	Operating: 20G acceleration part to part, 11ms
Viewing Angle (U/D/R/L)	89/89/89/89	Certifications & Compliance	CE/FCC
Contrast Ratio	1200:1	Power Input	DC-24V 2.5A Max.
Touchscreen	10-point, PCAP, Anti-fingerprint coating	Power Consumption	Max. 60W
Bonding	Air bonding	<b>Mechanical</b>	
<b>I/O</b>		Weight	11.2 kg
USB Port	USB type B (for touch)	Dimensions (H x W x D)	755.3 x 447.9 x 53.8 mm
Video	DPx1, DVIx1, VGAx1	Mounting	VESA Mount, M6 200mm x 200mm (Standard)
Audio	w/o Audio		