



CONFIDENTIAL

VERTRAULICH

THIS DRAWING IS THE EXCLUSIVE PROPERTY OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsanmeldungen. Jede Verfuugungsbefugnis, wie Kopier- und Weitergaberecht, bei uns.



-		-				-		1006.1505-XX			
Figure		Type				Customer No.		Art.No.-PI			
General tolerances						Sheet 01			Ident. K	Document number 10061505	Index g
All dimensions are in millimetres	Shape and location 	Angle ± 2 °	Edge tolerance 		Length						
				0-6	± 0.1	± 0.2					
				>6-15	± 0.15	± 0.3					
				>15-30	± 0.2	± 0.5					
				>30-70	± 0.3	± 10%					
				>70-120	± 0.4						
>120	± 0.8										
g	134431	2020-10-22		HHE		Format DIN A4	Projection 	Scale 1:1	Snap action switch		
f	128297	2020-01-28		HHE							
e	109072	2017-08-17		TRIGUIK							
d	90078	2014-06-23		BRC					System NX V11.0		
Index	MEC-No.	Date (YYYY-MM-DD)		Edited by		Replacement of Zg.gl.Nr.v.02.09.1999					
											