




-		-						-			1006.4302-XX						
Figure		Type						Customer Part No.			Art.No.-PI						
Shape and location 		Angle $\pm 2^\circ$ Edge tolerance 		Length				Radii				Sheet 01			Ident. K	Document number 10064302	Index h
				0-6	± 0.1		$\pm$	0-6	± 0.2	Format DIN	Projection 	Scale 1:1					
				>6-15	± 0.15		$\pm$	>6-15	± 0.3								
				>15-30	± 0.2		$\pm$	>15-30	± 0.5								
				>30-70	± 0.3		$\pm$	>30-200	$\pm 10\%$								
				>70-120	± 0.4		$\pm$		$\pm$								
				>120-200	± 0.8		$\pm$		$\pm$								
					$\pm$		$\pm$		$\pm$								
	$\pm$		$\pm$		$\pm$												
										All dimensions are in millimetres			Snap action switch				
h	137878	2022-01-31		KELBOUSSIM		System NX V1872			Replacement of Zg.gl.Nr.v.13.11.1996			 MARQUARDT					
g	134431	2020-10-22		HHE													
f	128297	2020-01-29		HHE													
e	109072	2017-08-17		TRIGUIK													
Index	MEC-No.	Date (YYYY-MM-DD)		Edited by													