





Recommended terminal layout; side of component
Tolerances as per DIN IEC 326 item 3 very fine



Marking

168..
12 (8) / 250 ~ T100/55
10 (8) / 250 ~ 5E4




12A 125-250 VAC
1/2 HP 125-250 VAC
R97




SPST

Code of manufacture:
place/year/week

Suitable for appliances of class II



operating position	h
OFF	26.5
ON	23.8
block	22.2



-	-	-	1681.4101-XX
Figure	Type	Customer Part No.	Art.No.-PI
Shape and location 	Angle ± 2 ° Edge tolerance 	Sheet 01 Format DIN A4 Projection Scale 1:1 All dimensions are in millimetres	
		Ident. K	Document number 16814101
		Appliance Switch	
		MARQUARDT	
		Index	
		16814101-01-12-0-K-999 RELEASED/FREIGEgeben 2021/Aug/26	
		Index	
		Index	
		Index	
		Index	