

CONFIDENTIAL





VERTRAULICH

THIS DRAWING IS THE EXCLUSIVE PROPERTY
OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY
NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

Alle Rechte bei Marquardt, auch fuer den
Fall von Schutzrechtsanmeldungen. Jede Veruegungs-
befugnis, wie Kopier- und Weitergaberecht, bei uns.

©

A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
		0.75 to 1.25	19.2-0.1	12.9+0.1
		1.25 to 2	19.4-0.1	12.9+0.1
B				
C				
D				
E				




Marking

1801.
4(2) /250 ~ T100/55

6A 125V AC
4A 250V AC
1/10HP 125-250V AC
R52

SPNC
Suitable for appliances of class II



-	-	-	1801.1302-XX
Figure	Type	Customer Part No.	Art.No.-PI
Shape and location	Angle $\pm 2^\circ$	Sheet 01	
	Edge tolerance	Ident.	Document number
		K	18011302
		Appliance Switch	
d	137838	2021-08-13	JOSHIO
c	29977	2000-11-15	GRH
b	15837	1984-04-10	RIE
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
		System NX V1872	Replacement of
		Zg.gl.Nr.v.31.05.1978	
MARQUARDT			