





A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness 0.75 to 1.25 1.25 to 2 2 to 3	length of cut-out 19.2 -0.1 19.4 -0.1 19.8 -0.1	width of cut-out 21.9 +0.1 21.9 +0.1 21.9 +0.1
B				
C				
D				
E	Marking 1802. 6A 125-250V AC 1/4HP 125V AC 1/2HP 250V AC R30 DPST suitable for appliances of class II G=matching IEC 60335-1:2001 clause 30 Code of manufacture: place/year/month On box: G			



-		-				-		1802.1117-XX							
Figure		Type				Customer Part No.		Art.No.-PI							
Shape and location 		Angle ± 2 °		Length				Radii		Sheet 01			Ident. K	Document number 18021117	Index d
				0-6		± 0.2		±	0-6	± 0.2	Format DIN A4	Projection 			
		>6-15		± 0.4		±	>6-15	±							
		>15-30		± 0.4		±	>15-30	±							
		>30-70		±		±	>30-200	±							
		>70-120		±		±		±							
		>120-200		±		±		±							
				±		±		±							
				±		±		±							
				±		±		±							
d	137845	2023-02-14		MUT		All dimensions are in millimetres			Appliance Switch						
c	102505	2016-09-06		MUT											
b	98181	2015-10-28		MUT											
a	63899	2010-03-11		MUT											
Index	MEC-No.	Date (YYYY-MM-DD)		Edited by		System NX V1899			 MARQUARDT						
						Replacement of Zg.gl.Nr.v.23.02.2005									