






A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
		0.75 to 1.25	19.2 -0.1	21.9+0.1
		1.25 to 2	19.4 -0.1	21.9+0.1
		2 to 3	19.8 -0.1	21.9+0.1



Marking



1805.
6(4)/250~5E4 T100/55
10(4)/250~
5/50A 250V~





6A 250V AC
1/2 HP
R 87 

Code of manufacture: place/year/week

DPST

Neon lamp with Rv for 230V AC
Suitable for appliances of class II



-		-						-		1805.7104-XX			
Figure		Type						Customer Part No.		Art.No.-PI			
Shape and location  Angle ± 2 ° Edge tolerance 								Sheet 01			Ident. K	Document number 18057104	Index b
								Format DIN	Projection	Scale			
								A4		1:1	Appliance Switch		
								All dimensions are in millimetres					
								System NX V1872					
								Replacement of Zg.gl.Nr.v.25.03.1997					
b	137893	2021-06-07		JOSHIO									
a	46930	2006-04-04		VOR									
		1997-03-25											
Index	MEC-No.	Date (YYYY-MM-DD)		Edited by									