





A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
		0.75 to 1.25	19.2-0.1	12.9+0.1
		1.25 to 2	19.4-0.1	12.9+0.1
B				
C				
D				
E				



SPDT
Suitable for appliances of class II

Marking



1813.

6(4)/250~5E4

10(4)/250~ T100/55



6A 125-250V AC


1/4HP 125V AC

1/2HP 250V AC

R30



Code of manufacture: place/year/week



-	-	-	1813.1102-XX
Figure	Type	Customer Part No.	Art.No.-PI
Shape and location	Angle $\pm 2^\circ$	Sheet 01	
	Edge tolerance	Ident.	Document number
		K	18131102
		Appliance Switch	
f	137894	2021-06-09	JOSHIO
e	80769	2012-10-23	MUT
d	64505	2010-01-26	MUT
c	29862	2000-06-19	BMI
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
		Format DIN	Projection
		A4	1:1
		All dimensions are in millimetres	
		System	NX V1872
		Replacement of	Zg.gl.Nr.v.29.06.2000
		MARQUARDT	