







Upper part and bottom part
Material: Polyamide
Color: black, similar RAL 9011

Operating position at the travel of (measured at start position) ~ 8 mm measured at outer edge of upper part

Schematic




Two single pole normally open

Marking

© MARQUARDT
2410.1001 μ
6(2.5)/250~50E3

Schematic



-		-		-		2410.1001-XX			
Figure		Type		Customer Part No.		Art.No.-PI			
Shape and location ⊙ = 	Angle ± ° Edge tolerance	Length		Radii		Sheet 01			
		0-6	+ 0.15		+ 0.6		Format DIN	Projection	Scale
		P6-15	+ 1		P6-15		A2		1:1
		>15-30	+ 1		>15-30		All dimensions are in millimetres		
		>30-70	+ 1.5		>30-70				
		>70-120	+ 1.5						
		>120-200							
		k	137878	2022-02-01	KELBOUSSIM	System NX V1872			
		j	131778	2020-10-31	THAKARES				
i	30221	2000-09-27	PFU						
h	23889	1996-05-08	MOO						
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by	Replacement of Zg.gl.Nr.v.06.05.1994					
						 MARQUARDT			