







1	2	3	4		
A B C D E					
 					
SINGLE WIRE SEAL Einzel-Dichtungs-System CONTACT BODY PRE-SILVER PLATED MIN 0.8µm CONTACT ZONE SELECTIVE PRE-SILVER PLATED MIN 3µm Kontaktkörper vorversilbert min 0.8µm Kontaktzone selektiv vorversilbert min 3µm					
SECTION A-A Schnitt A-A  E = 3.6 G = 3.8 D = 1.8	SECTION B-B Schnitt B-B  H = 5.4 K = 4.6 D = 3.2	WIRE CRIMP Drhttermins  2.5mm² = 1.77 2.0mm² = 1.64 1.5mm² = 1.51	SECTION A-A Schnitt A-A  E = 2.8 G = 3.9 D = 1.7	SECTION B-B Schnitt B-B  H = 4.8 K = 4.2 R = 2.8	
a AMP-Order-No. 929938-6 FURTHER INFORMATION SEE TYCO DRAWING NR: C-1355046 Weitere Informationen siehe Tyco Zeichnung Nr.: C-1355046					
fuer Form und Lage FOR SHAPE AND LOC. ☉ =		Allgemeintoleranzen UNTOLERANCED DIMENSIONS PROJEKTION Abmasse und Nennmassbereiche Angaben in mm Laengen LENGTH Radien RADII 0-6 ± ± >6-15 ± ± >15-30 ± ± >30-70 ± ± >70-120 ± ± >120-200 ± ± ALL DIMENSIONS ARE IN MILLIMETRES		Pause COPY Blatt SHEET 01 Original DIN A4 Masstab SCALE 2:1 0 10 20 30mm	Typ K Zeichn./DRAWING NO. 288029011 Index a
a 70353 07.09.10 FEV 68840 22.07.10 FEV		CAD: CATIA_V5 gez./DRAWN BY 06.07.10 FEV gepr./CHECKED BY Ersatz fuer/REPLACEMENT OF		JPT STECKER  MARQUARDT	
Ausg. ISSUE	Aenderung REVISION	gez. DRAWN BY	Ausg. ISSUE	Aenderung REVISION	gez. DRAWN BY