

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190720055

Status:

Active

Overview:

Solderless Terminals

Description:

VibraKrimp Ring Tongue Terminal for 18 to 22 AWG Wire, Stud Size 2 (M2), Length 16.69mm

Documents:	
Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
Product Specification PS-19902-011-001 (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19072
Crimp Quality Equipment	Yes
Overview	Solderless Terminals
Product Name	VibraKrimp
Type	Ring
UPC	800753074002
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.793/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	2 (M2)
Wire Size AWG	14, 16
Material Info	
Engineering Number	BB-423-04
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	190720046-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19072 Series

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Crimp Hand Tool

640016800

Crimp Head for the AT-200 Pneumatic Hand Tool

640056800

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19072-0055