






Comparison Guide



Multi-Range DC Power Supplies 9240 Series

Company	B&K Precision					Keysight		Chroma	
Model	9240	9241	9242	9172B	9201B	E36231A	E36232A	62010L-36-7	62015L-60-6
									
List price	\$1,225		\$1,475	\$1,115	\$890	\$1,957		\$1,688	\$1,749
Output Power	120 W		200 W	105 W	200 W	200 W		108 W	150 W
Form Factor	2U x 1/2			2U x 1/2		3U x 1/2		2U x 1/2	
Cost-Per-Watt	\$10.21		\$7.38	\$10.62	\$4.45	\$9.79		\$15.63	\$11.66
Output Characteristics									
Max Output Voltage	32 V	60 V		35 V / 70 V	60 V	30 V	60 V	36 V	60 V
Max Output Current	8 A	4 A	10 A	3 A / 1.5 A	10 A	20 A	10 A	7 A	6 A
Load Regulation	≤ 0.01% + 3 mV			≤ 0.01% + 1 mV	≤ 0.01% + 8 mV	< 0.01% + 2 mV		< 0.01% + 2 mV	
Ripple and Noise (20 Hz to 20 MHz)	≤ 5 mVpp	≤ 10 mVpp		≤ 5 mVpp	≤ 8 mVpp	< 4.5 mVpp	< 3.5 mVpp	< 2 mVpp	< 3 mVpp
Programming Accuracy (Voltage)	0.03% + 4 mV	0.03% + 8 mV		≤ 0.05% + 10 mV	≤ 0.03% + 5 mV	0.03% + 4 mV	0.03% + 8 mV	0.05% + 10 mV	
Features									
LED Mode	✓			✓	-	-		-	
Data Logging to USB	✓			-		✓		-	
Configurable Battery Charge Mode	✓			-		-		-	
Front Panel Sense	✓			✓	-	✓		✓	
List Mode Programming	✓			✓ Limited		✓		✓	
General									
I/O Interfaces	USB (TMC/VCP), LAN (LXI), (GPIB model option +\$220)			USB, (GPIB/LAN +\$165), (RS232 +\$60)	USBTMC-compliant, RS232	USBTMC, LAN (LXI), (GPIB option +\$365)		USBTMC and LAN	
NRTL ⁽¹⁾ Mark	cTUVus certification mark			-		CSA certification mark		-	
Warranty	3 years			3 years		3 years		1 years	

⁽¹⁾ Nationally recognized test laboratory such as UL, CSA, TUV