

CAPAROC parts for hazardous locations

Class I, Division 2 rated parts (CID2)						
Part number	Part type	Description	Approvals			
1-channel circuit breakers			UL 508	UL 2367	NEC Class 2	CID2
1115415	CAPAROC E1 12-24DC/1-4A	1-channel electronic circuit breaker module, adjustable nominal current from 1 A to 4 A, NEC Class 2	X	X	X	X
1115649	CAPAROC E1 12-24DC/1-10A	1-channel electronic circuit breaker module, adjustable nominal current from 1 A to 10 A	X	X		X
1157288	CAPAROC E1 12-24DC/1A	1-channel electronic circuit breaker module, with fixed nominal current of 1 A, NEC Class 2	X	X	X	X
1157290	CAPAROC E1 12-24DC/2A	1-channel electronic circuit breaker module, with fixed nominal current of 2 A, NEC Class 2	X	X	X	X
1157285	CAPAROC E1 12-24DC/4A	1-channel electronic circuit breaker module, with fixed nominal current of 4 A, NEC Class 2	X	X	X	X
1157286	CAPAROC E1 12-24DC/6A	1-channel electronic circuit breaker module, with fixed nominal current of 6 A	X	X		X
1157279	CAPAROC E1 12-24DC/8A	1-channel electronic circuit breaker module, with fixed nominal current of 8 A	X	X		X
1157284	CAPAROC E1 12-24DC/10A	1-channel electronic circuit breaker module, with fixed nominal current of 10 A	X	X		X
2-channel circuit breakers			UL 508	UL 2367	NEC Class 2	CID2
1115655	CAPAROC E2 12-24DC/1-4A	2-channel electronic circuit breaker module, adjustable nominal current from 1 A to 4 A, NEC Class 2	X	X	X	X
1110984	CAPAROC E2 12-24DC/2-10A	2-channel electronic circuit breaker module, adjustable nominal current from 2 A to 10 A	X	X		X
Current Rails			UL 508	UL 2367	NEC Class 2	CID2
1110989	CAPAROC CR 20	20 position current rail, for installation on a DIN rail	X			X
1115672	CAPAROC CR 8	8 position current rail, for installation on a DIN rail	X			X
1115674	CAPAROC CR EXT20	Extension 20 position current rail, for installation on a DIN rail	X			X
1110990	CAPAROC CR EXT8	Extension 8 position current rail, for installation on a DIN rail	X			X
1110991	CAPAROC CR EXT4	Extension 4 position current rail, for installation on a DIN rail	X			X
Power Modules			UL 508	UL 2367	NEC Class 2	CID2
1115661	CAPAROC PM S-R	Status-reset Power module with status output and reset input	X			X
1110986	CAPAROC PM PN	PROFINET Power module with PROFINET interface	X			X
Distribution Module			UL 508	UL 2367	NEC Class 2	CID2
1110987	CAPAROC PD 0V	0V Distribution module	X			X

Triple rated parts: CID2, ATEX and IECex							
Part number	Part type	Description	Approvals				
2-channel circuit breakers			UL 508	UL 2367	NEC Class 2	CID2	ATEX
1344361	CAPAROC E2 12-24DC/1-4A EX	2-channel electronic circuit breaker module, adjustable nominal current from 1A to 4A, for 12 VDC to 24 VDC applications. Triple rated for hazardous locations: CID2, ATEX, IECex	X	X	X	X	X
1344364	CAPAROC E2 12-24DC/2-10A EX	2-channel electronic circuit breaker module, adjustable nominal current from 1A to 10A, for 12 VDC to 24 VDC applications. Triple rated for hazardous locations: CID2, ATEX, IECex	X	X		X	X
Power Module			UL 508	UL 2367	NEC Class 2	CID2	ATEX
1344363	CAPAROC PM S-R EX	Status-reset Power module with status output and reset input, for 12 VDC to 24VDC applications. Triple rated for hazardous location: CID2, ATEX, IECex	X			X	X