

				
	Stainless Steel Tie, 14.3" Long, 202lb Tensile Strength, SS304, Metal, 100/pkg	Stainless Steel Tie, 7.9" Long, 202lb Tensile Strength, SS304, Metal, 100/pkg	Stainless Steel Tie, 20.5" Long, 202lb Tensile Strength, SS304, Metal, 100/pkg	Stainless Steel Tie, 27" Long, 202lb Tensile Strength, SS304, Metal, 100/pkg
Short Description	Stainless Steel Tie, 14.3" Long, 202lb Tensile Strength, SS304, Metal, 100/pkg	Stainless Steel Tie, 7.9" Long, 202lb Tensile Strength, SS304, Metal, 100/pkg	Stainless Steel Tie, 20.5" Long, 202lb Tensile Strength, SS304, Metal, 100/pkg	Stainless Steel Tie, 27" Long, 202lb Tensile Strength, SS304, Metal, 100/pkg
Part No.	MBT14S-S	MBT8S-S	MBT20S-S	MBT27S-S
Article No.	111-93148	111-93088	111-93208	111-93278
Min. Tensile Strength (Imperial)	202	202	202	202
Length (L) (Imperial)	14.3	7.9	20.5	27
Length (L) (Metric)	362	201	521	685
Width (W) (Imperial)	0.18	0.18	0.18	0.18
Width (W) (Metric)	4.6	4.6	4.6	4.6
Bundle Ø Max. (Imperial)	4	2	6	8
Bundle Ø Max. (Metric)	102	50	152	203
Bundle Ø Min. (Imperial)	0.67	0.67	0.67	0.67
Min. Bundle Ø (Metric)	17	17	17	17
Color	Metal (ML)	Metal (ML)	Metal (ML)	Metal (ML)
Material	Stainless Steel (SS304)	Stainless Steel (SS304)	Stainless Steel (SS304)	Stainless Steel (SS304)
Flammability	Non-burning	Non-burning	Non-burning	Non-burning
Operating Temperature (Metric)	0	0	0	0
Variant	Not Serrated	Not Serrated	Not Serrated	Not Serrated
Pkg. Qty.	100	100	100	100
ROHS Conformity	Yes	Yes	Yes	Yes
Halogenfree	Yes	Yes	Yes	Yes
UV Resistant	Yes	Yes	Yes	Yes