

WIRE-TO-WIRE

Micro-Fit 3.0™ 3.00mm	5.0A
Mini-Fit Jr.™ 4.20mm	9.0A
.093" Pin & Socket 5.03mm / 6.70mm	12.0A
Mini-Fit® Plus 4.20mm	13.0A
Sabre™ 7.50mm	18.0A

PANEL-TO-PANEL

Micro-Fit BMI™ 3.00mm	5.0A
Mini-Fit® BMI 4.20mm	8.0A
Mini-Fit® Plus (Blindmating) 4.20mm	12.0A

WIRE-TO-BOARD

KK® 254 2.54mm	4.0A
Micro-Fit 3.0™ 3.00mm	5.0A
KK® 396 3.96mm	7.0A
Mini-Fit Jr.™ 4.20mm	9.0A
.093" Pin & Socket 5.03mm / 6.70mm	12.0A
Mini-Fit® Plus 4.20mm	12.5A
Sabre™ 7.25mm	18.0A
Mega-Fit 5.70mm	23.0A

BOARD-TO-BOARD

Micro-Fit BMI™ 3.00mm	5.0A
KK® 396 3.96mm	5.0A
Mini-Fit® BMI 4.20mm	8.0A
Mini-Fit® Plus 4.20mm	11.0A

PANEL-TO-BOARD

Micro-Fit BMI™ 3.00mm	5.0A
Mini-Fit® BMI 4.20mm	8.0A
Mini-Fit® Plus (Blindmating) 4.20mm	11.5A