

Woodhead ArcArrest 30A and 60A Switch-Rated Connector System >

Incorporating many options and components into a smooth, contoured design, the Woodhead ArcArrest Switch-Rated Connector System delivers the simplest and fastest way to de-energize industrial equipment and perform Lockout/Tagout operations

FEATURES AND ADVANTAGES

Inclusion of options such as MAX-LOC cord-grip technology, finger drawplates, lock-out holes and plug caps in a smooth, contoured design

Reduces user costs and simplifies ordering. Enhances cleanability in food-processing and other harsh environments. Delivers enhanced durability for use in the toughest industrial applications

Furnace-brazed contact tips

Produces tips with superior flatness and positioning accuracy compared to the flame brazing process used by competitors

Laser labelling

Provides a clean and permanent record of certifications and specifications.

NEMA 4X and IP69k rated

Eliminates ingress of dust and water in a variety of harsh industrial environments. Sealing is automatic when connected



Woodhead ArcArrest Switch-Rated Connector

Non-Fused Disconnect Switch

Woodhead ArcArrest 30A and 60A Switch-Rated Connector System >

FAST AND POSITIVE LOCK-OUT

Plug and receptacle are easily locked out to provide fast and positive lock-out/tag-out of machinery.*



Lock-out hole in male plug designed for 1/4" or 5/16" lock shank diameter

* Locks not included.



Lock-out hole in receptacle designed specifically for 1/4" lock shank diameter

WHAT IS A SWITCH-RATED CONNECTOR AND UL 2682?

Unlike standard connectors, switch-rated devices listed under UL 2682 can operate as switches and be used to disconnect loads while energized. When operated under load, arcing will occur between the male and female contacts, which they can withstand without damage. The user is completely shielded from this energy because the plug maintains a connection with the receptacle during operation. A twisting motion must be applied by the user to remove the plug after the circuit has been interrupted.

www.molex.com/link/arcarrest.html