

AC/DC VOLTAGE TESTERS

ET40



3 m
IP41

CAT III
250V

ETL
Intertek
5001748

CE

ET45



3 m
IP44

CAT III
350V

ETL
Intertek
5001748

CE


**KLEIN
TOOLS®**



ET40, ET45 VOLTAGE TESTERS

Klein Tools' ET40 and ET45 Voltage Testers were designed as simple, easy to use testers for checking, verifying or troubleshooting common residential electrical wiring and devices such as outlets, light fixtures, doorbells, batteries and more! Bright LED's illuminate to indicate voltage levels detected. Convenient features on both models include four levels of voltage testing, built-in test lead holders (for attached leads) and convenient pocket clip for carrying. The ET45 does NOT require batteries as it is powered by the source being tested! The ET40 (uses two AAA batteries) and features indicators for positive and negative DC polarity, and tests DC voltages as low as 1.5V.


ET40 Electronic AC/DC Voltage Tester



- Test voltage at four AC or DC levels:
 - AC: 12V, 24V, 120V, 240V
 - DC: 1.5V, 9V, 12V, 17-24V
- DC polarity indicators
- 2x AAA batteries included



ET45 Electronic AC/DC Voltage Tester



- **NO BATTERIES REQUIRED!**
- Test voltage at four levels:
 - AC: 24V, 48V, 120V, 240V
 - DC: 32V, 64V, 160V, 330V
- Test lead holders spaced for testing tamper-resistant US-style outlets



Cat. No.	UPC# 0-92644+	Description	Height	Weight
ET40	69183-6	Electronic AC/DC Voltage Tester	5.24" (133mm)	3.1 oz (90g)
ET45	69184-3	AC/DC Voltage Tester	4.45" (113 mm)	1.8 oz (52 g)



See our complete line of **Test & Measure** products
www.kleintools.com

