



TE Connectivity / DEUTSCH DT Series Connectors Modifications

- B016: Receptacle has extended shell and enhanced keys, plug has enhanced seal retention (P012), 12 way
- BE02: Receptacle with extended shell and enhanced keys (B016), end cap
- BE03: Receptacle with extended shell and enhanced keys (B016), end cap, black
- BE04: Receptacle with extended shell and enhanced keys (B016), end cap, reduced diameter seals (E seal), black
- BE05: Receptacle with extended shell and enhanced keys (B016), end cap, sealed flange, reduced diameter seals (E seal), threaded stainless steel flange inserts
- BL04: Receptacle with extended shell and enhanced keys (B016), welded flange
- BL08: Receptacle with extended shell and enhanced keys (B016), welded flange, black
- BL10: Receptacle with extended shell and enhanced keys (B016), sealed flange, reduced diameter seals (E seal), shrink boot adapter, threaded stainless steel flange inserts
- BL11: Receptacle with extended shell and enhanced keys (B016), sealed flange, reduced diameter seals (E seal), end cap, threaded stainless steel flange inserts
- C008: Cavity blocked (C)
- C015: Reduced diameter seals (E seal)
- C017: Solid rear grommet
- CE01: Reduced diameter seals (E seal), end cap
- CE02: Reduced diameter seals (E seal), black
- CE03: Reduced diameter seals (E seal), end cap, black
- CE04: Reduced diameter seals (E seal), shrink boot adapter
- CE05: Plug with reduced diameter seals (E seal), enhanced seal retention (P012), end cap
- CE06: Plug with reduced diameter seals (E seal), enhanced seal retention (P012)
- CE07: Receptacle with extended shell and enhanced keys (B016), reduced diameter seals (E seal), end cap
- CE08: Receptacle with extended shell and enhanced keys (B016), reduced diameter seals (E seal)
- CE09: Reduced diameter seals (E seal), shrink boot adapter, black
- CE10: Plug with reduced diameter seals (E seal), enhanced seal retention (P012), black
- CE11: Plug with reduced diameter seals (E seal), enhanced seal retention (P012), end cap, black
- CE12: Plug with reduced diameter seals (E seal), enhanced seal retention (P012), shrink boot adapter, black
- CE13: Plug with reduced diameter seals (E seal), enhanced seal retention (P012), shrink boot adapter
- CE14: Plug with reduced diameter seals (E seal), enhanced seal retention (P012), latch guard end cap, black

CE27: Plug with reduced diameter seals (E seal), enhanced seal retention (P012), for use with integrated LED wedgelock, end cap, transparent Ultem
CE28: Plug with reduced diameter seals (E seal), enhanced seal retention (P012), for use with integrated LED wedgelock, transparent Ultem
CL03: Reduced diameter seals (E seal), welded flange
CL07: Reduced diameter seals (E seal), sealed flange, shrink boot adapter
CL08: Reduced diameter seals (E seal), welded flange, end cap, disabled latch
CL09: Reduced diameter seals (E seal), sealed flange, end cap, black
CL15: Reduced diameter seals (E seal), welded flange, black
CP01: All cavities plugged, enhanced seal retention (P012), end cap
E003: End cap
E004: Black
E005: Black, end cap
E008: Shrink boot adapter
EE01: Shrink boot adapter, black
EE05: High temp, enhanced seal retention (P012) on plug, end cap, black
EF01: Fluorosilicone front seals, end cap
EF02: Fluorosilicone front seals, latch guard end cap
EK02: Plug, 18 cavity DT with 18 size 16 contacts, enhanced seal retention (P012), end cap, "A" key is gray, "B" key is black, "C" key is green, "D" key is brown
EP04: End cap (same as E003 mod)
EP05: Latch guard end cap
EP06: Plug with enhanced seal retention (P012), end cap
EP07: Plug with enhanced seal retention (P012), black
EP08: Plug with enhanced seal retention (P012), end cap, black
EP09: Plug with enhanced seal retention (P012), latch guard end cap, black
EP10: 120 ohm terminating resistor (J1939), black
EP11: Plug with enhanced seal retention (P012), shrink boot adapter, black
EP12: Bussed receptacle, 4 and 6 way only, 1 buss, black, gold plated pins
EP13: Bussed receptacle, 4 and 6 way only, 1 buss, black, nickel plated pins
EP14: Bussed receptacle, 6 way, 2 busses, black, nickel plated pins
EP20: Plug with enhanced seal retention (P012), shrink boot adapter
L012: Welded flange
LE01: Sealed flange, inside mount, gasket, end cap
LE03: Sealed flange, outside mount, o-ring sold separately, end cap, NOTE: DT04-08PA-LE03 comes with shrink boot adapter and o-ring on flange
LE05: Sealed flange, inside mount, gasket, end cap

LE06: Sealed flange, inside mount, reduced diameter seals (E seal), end cap
LE07: Welded flange, end cap
LE08: Welded flange, shrink boot adapter, gray
LE09: Sealed flange, o-ring, end cap, black
LE10: Sealed flange, inside mount, gasket, end cap, black
LE11: Welded flange, end cap, black
LE12: Welded flange, shrink boot adapter, black
LE13: Special adapter, round housing, end cap
LE14: Welded flange, black
LE17: Receptacle with extended shell and enhanced keys (B016), sealed flange, gasket sold separately, end cap, black
LE21: Receptacle with extended shell and enhanced keys (B016), sealed flange, reduced diameter seals (E seal), end cap, one piece connector design, threaded stainless steel flange inserts
N006: Receptacle with 90° molded-in contacts
P006: 120 ohm terminating resistor (J1939)
P007: Receptacle “Y” connector (J1939)
P012: Plug with enhanced seal retention, 2-6 way are black, 8 and 12 way “A” key is gray, “B” key is black, “C” key is green, “D” key is brown
P016: Bussed receptacle, 12 way, gold plated contacts
P021: Bussed receptacle, 6, 8, and 12 way, one buss, nickel plated pins
P026: Bussed receptacle, 8 and 12 way, two busses, nickel plated pins
P027: Bussed receptacle, 12 way, two busses, gold plated pins
P028: Bussed receptacle, 8 way, two busses, nickel plated pins
P030: Bussed receptacle, 12 way, four busses, nickel plated pins
P031: Bussed receptacle, 12 way, four busses, gold plated pins
P032: Integrated shrink boot adapter (J1939), black
P060: Bussed receptacle, 2 way, one buss, nickel plated pins
P075: Bussed receptacle, 12 way, three busses, nickel plated pins
PE01: Latch guard, 120 ohm terminating resistor (J1939)
PP01: Plug with enhanced seal retention (P012), 120 ohm terminating resistor (J1939), end cap, black
RT01: Receptacle with MUR 460 diode
RT02: Receptacle with 1N5625GP diode
RT03: Receptacle with MUR 460 diode, 4 way available
RT06: Receptacle with Phillips T.V.S diode 1.5KE130CA, green
RT25: Receptacle with 27k ohm resistor, black

DTM Series Modification Types

C017: Solid rear grommet

E003: End cap

E004: Black

E005: Black, end cap

E007: Shrink boot adapter

EE03: Shrink boot adapter, black

EE04: High temp, black

EP10: 120 ohm terminating resistor (J1939), black

L012: Welded flange

DTP Series Modification Types

C015: Reduced diameter seals (E seal)

C017: Solid rear grommet

CE02: Reduced diameter seals (E seal), black

E003: End cap

E004: Black

E005: Black, end cap

L012: Welded flange

LE07: Welded flange, end cap

P018: Receptacle with 12 AWG wires attached