

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39100-0812](#)
Status: **Active**
Overview: Eurostyle™ Two-Screw Barrier Strips
Description: 8.00mm Pitch Beau™ Eurostyle™ Two-Screw Terminal Strips, 12 Circuits
Replacement Part Number: 39100-1812

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 228650
 UL E48521

General

Product Family Terminal Blocks
 Series [39100](#)
 Application Wire-to-Wire
 Component Type One Piece
 Overview [Eurostyle™ Two-Screw Barrier Strips](#)
 Product Name Eurostyle™ Two Screw
 Replacement Part Number [39100-1812](#)
 Type Barrier Strip
 UPC 822348694303

Physical

Circuits (Loaded) 12
 Entry Angle Horizontal
 Lock to Mating Part None
 Number of Rows 2
 Orientation Vertical
 PCB Retention Yes
 Panel Mount Mounting Holes Between Circuit
 Pitch - Mating Interface 8.00mm
 Pitch - Termination Interface 8.00mm
 Polarized to Mating Part No
 Stackable No
 Temperature Range - Operating 100°C
 Wire Size AWG 12, 14, 16, 18, 20, 22


Electrical

Current - Maximum per Contact 20A
 Voltage - Maximum 600V

Material Info

Reference - Drawing Numbers

Sales Drawing SD-39100-002



EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Pb

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[39100Series](#)