


Light Shield Incandescent Indicators



T-1 3/4
MIDGET
FLANGE BASE

See lamp ratings
on page J.

ONE TERMINAL – FULLY INSULATED for use on grounded circuits.

FOR FRONT MOUNTING IN 15/32" CLEARANCE HOLE

MEET OR EXCEED ENVIRONMENTAL AND OPERATIONAL REQUIREMENTS
OF MIL-L-7806 AND MIL-L-3661

An opening in the side of the metal lamp holder emits light on the panel to illuminate dials or controls. The usual opening is 1/4" X 5/32". The 113 series has a molded colored filter to provide a colored light †.

How to designate the Three Digit Part Number Suffix (-XXX)
(4 Series only)

Finish	Resistor	Hardware
1—white nickel	0—none	1 — brass
2—black nickel		3 — water tight on face of panel (113 Series only)
3—polished chrome		7 — insulated mounting*

Example: 4-1930-2900-101 (white nickel finish, no resistor, brass hardware).

† For 2 terminal requirements, assembly is supplied with 2 insulating washers and a lug. Mounting hole becomes 9/16".

MATERIALS AND FINISHES

- **Mounting Bushing:** Standard— Brass, black nickel finish. Optional, (4 series only)— Polished chrome or white nickel finish.
- **Mounting Nut:** Brass, white nickel finish.
- **Internal-tooth Lockwasher:** Phosphor bronze, white nickel finish.
- **Terminals:** Soldering— Brass, hot tin dip. Screw— Brass, cadmium plated with yellow iridescent chromate finish.
- **Insulation:** Per MIL-L-7806.

4 SERIES 113 SERIES



4-1930-2900-201 (without filter)



113-1830-2931-201 (with molded filter)

BASE PART NUMBERS

solder terminal	screw terminal
4-1930-29-201	4-1830-29-201

CAP PART NUMBERS

COMPLETE ASSEMBLY PART NUMBERS

<p>4-2900-200 (without filter)</p>	4-1930-2900-201	4-1830-2900-201
<p>113-2931-200 (with molded filter)</p>	113-1930-2931-201	113-1830-2931-201

*Filter colors: The digit before the three digit part number suffix indicates that the filter is RED. When a color other than red is desired, change this digit as follows: Red-1; Green-2; Yellow (amber)-3; Blue-4; Clear (colorless)-7. Example: 113-1930-2934-201 (Blue).

Part numbers shown in gray are normally in inventory at your Dialight Distributor.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[113-2937-203](#) [113-2931-200](#) [004-1930-29-207](#) [113-2931-203](#) [004-1830-29-207](#) [113-2937-200](#) [113-2934-203](#) [004-1830-29-301](#) [113-2932-200](#) [113-2934-200](#) [004-1830-29-200](#) [004-1830-29-201](#) [004-1830-29-203](#) [004-1830-29-300](#)
[004-1930-29-200](#) [004-1930-29-201](#) [004-1930-29-203](#) [004-2900-300](#)