



AD40B Digital Ammeter

- Low-cost, miniature digital ammeter
- 400 A AC range
- 4000-count display with bargraph
- Autoranging
- Data Hold
- Auto-off
- 10mA resolution



No hassle warranty

No waiting.

*No shipping
charges.*



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)

Included Accessories
Carrying case and users manual



AD40B Digital Ammeter**Data Sheet****General Specifications**

Display	3-3/4 digit LCD (max reading 3999)
Overrange Indication	"OL" indicated
Low Battery Indication	Battery symbol
Power Supply	Two (2) 1.5 V AAA batteries (UM-4)
Battery Life	Alkaline 300 hours, approx.
Maximum Jaw Opening	25.4 mm
Dimensions (WxHxD)	64 x 190 x 36 mm
Weight	250 g (incl. Battery)
Operating Temperature:	0 °C to +40 °C, < 80 % R.H. non-condensing
Storage Temperature	-10 °C to +60 °C, < 70 % R.H. non-condensing, batteries removed
Safety	EN61010-1:2001, EN61010-2-32, Pollution Degree 2
Over Voltage Category	CAT III - 600V

Specifications (23°C±5°C, <80% R.H. non-condensing)

Function	Range	Accuracy
AC Current		
	40 A, 400 A	± (2 % rdg + 10 digits)
Resolution	0.01 A in 40 A range	
Overload Protection	660 A for AC current	

Amprobe® Test Tools

website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
tel: 877-AMPROBE

Amprobe® Test Tools Europe

In den Engematten 14
79286 Glottertal, Germany
Tel.: +49 (0) 7684 8009 - 0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[AD40B](#)