



JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	MSCP $\pm 25\%$	LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
266	2.5	.350	.200	2.51	20,000	C-2R
253	2.5	.350	LENS	END	20,000	C-2R
FG23	5.0	.020	.020	0.25	50,000	C-2R
3152	5.0	.060	.150	1.89	5,000	C-2R
7348	5.0	.115	.150	1.89	40,000	C-2R
8705	6.0	.040	.030	0.38	10,000	C-2V
337	6.0	.200	.630	7.92	1,000	C-2R
7351	6.3	.040	.030	0.38	20,000	C-2V
8708	6.3	.075	.230	2.89	1,000	C-2R
379	6.3	.200	.400	5.03	50,000	C-2F
398	6.3	.200	.550	6.91	5,000	C-2R
709	10.0	.014	.004	0.05	50,000	C-2F
397	10.0	.040	.080	1.01	30,000	C-2F
7354	12.0	.040	.120	1.51	10,000	C-2F
386	14.0	.080	.300	3.77	50,000	C-2F
336	14.0	.080	.500	6.29	2,500	C-2F
346	18.0	.040	.150	1.89	10,000	C-2F
7355	28.0	.040	.200	2.51	50,000	C-2F
388	28.0	.040	.300	3.77	25,000	C-2F
334	28.0	.040	.340	4.27	4,000	C-2F
7356	28.0	.065	.650	8.17	5,000	C-2F

METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0	 JKL COMPONENTS CORPORATION			
		TITLE T-1 3/4 STANDARD MIDGET GROOVE			
DRAWN BY L. WENGSTROM	APPVD BY DATE J.K. 8/2/05	SIZE A	FSCM NO. 55335	DRAWING NO. GROOVE BASE T-1 3/4	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE	RELEASED DATE 10/11/00	REVISION DATE 8/2/05	REV. NO. A SHEET 1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
A	DELETED PART #'S 393, 457, 276 RELEASE & CANCEL 7346, 7347	8/2/050 10/11/00

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

JKL Components:

[337](#) [386](#) [388](#) [7354](#) [7355](#) [8705](#) [266](#) [336](#) [346](#) [397](#) [709](#) [7351](#) [7356](#) [8708](#) [3152](#) [379](#) [334](#) [7348](#)