



Features

- PICMG® 1.0 Full-Size SBC
- Supports up to 1066 MHz FSB LGA775 Intel® Core™2 Duo processor
- Intel® Q965 + ICH8 chipset with Dual-Channel DDR2 667/533 MHz
- Supports PCI Express® x1 Gigabit Ethernet port

Specifications

Processor & System

CPU	Intel® Core™2 Duo E6400, 2.13GHz, 1066MHz FSB, 2MB L2 Cache, 65nm, 65W TDP, LGA775 Intel® Core™2 Duo E4300, 1.8GHz, 800MHz FSB, 2MB L2 Cache, 65nm, 65W TDP, LGA775 Intel® Pentium® Dual Core E2160, 1.8GHz, 800MHz FSB, 1MB L2 Cache, 65nm, 65W TDP, LGA775 Intel® Celeron® 440, 2.0GHz, 800MHz FSB, 512KB L2 Cache, 65nm, 35W TDP, LGA775 Intel® Pentium® 4 651, 3.4GHz, 800MHz FSB, 2MB L2 Cache, 65nm, 95W TDP, LGA775 Intel® Celeron® D 352, 3.2GHz, 533MHz FSB, 512KB L2 Cache, 65nm, 95W TDP, LGA775
Chipset	Intel® Q965 + Intel® ICH8 chipset
Memory	Dual-Channel DDR2 800/667/533 MHz, up to 4 GB
BIOS	Award 8 Mb flash memory
Watchdog Timer	1-255 sec. or min. software programmable and can generate system reset
Hardware Monitor	CPU/System temperature, fan speed and onboard DC voltages
Operating Systems	Windows® XP, 7 32/64-bit, Server 2003 Fedora™ Core 7

I/O Interfaces

IDE (PATA)	1x UltraATA 66/100/133
Serial ATA	2x SATA 3 Gb/s ports
USB	4x USB 2.0 ports by onboard pin headers
KB/MS	1x PS/2 keyboard/mouse
Parallel Port	1x LPT
Serial Port	1x RS-232, 1x RS-232/422/485

Audio

Audio Codec	Realtek® ALC883 Codec
Interface	Audio pin header

Display

Graphics	Intel® 965 integrated VGA (GMA 3000)
----------	--------------------------------------

Ethernet

Controller	Onboard Marvell 88E8056 GbE controller
Interface	10/100/1000Base-T Gigabit Ethernet
Interface	x1 PCIe® bus
Wake On LAN	Yes

Mechanical and Environmental

Form Factor	Standard Full-Size PICMG® 1.0 SBC
Dimensions	338 mm x 122 mm (L x W)
Operating Temp.	0°C to 60°C
Storage Temp.	-20°C to 80°C
Certifications	CE, FCC Class A
Relative Humidity	10% to 90%, non-condensed

Ordering Information

Model Number	Description/Configuration
NuPRO-852LV	PICMG® 1.0 Full-Size LGA775 Intel® Core™2 Duo SBC with Q965, DDR II, GbE, SATA II, IDE
NuPRO-852DV	PICMG® 1.0 Full-Size LGA775 Intel® Core™2 Duo SBC with Q965, DDR II, Dual GbE, SATA II, IDE

Note 1: CPU, Memory module and Cooler kit are not included.

Optional Accessories

Model Number	Description/Configuration
LGA775 1U CPU Cooler	LGA775 1U Thermal Module
LGA775 3U CPU Cooler	LGA775 3U Thermal Module
Backplate	Backplate for 3U CPU cooler
Audio Cable	Audio Cable for NuPRO-852

Packing List

NuPRO-852	1x COM+Parallel port cables with bracket
1x Y-cable for PS/2 keyboard/mouse	2x SATA data cables
1x UltraATA 100 IDE cable	2x SATA power cables
1x USB 2.0 cable with bracket	Driver CD
1x COM port cable with bracket	User's manual

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[NuPRO-852LV](#) [NuPRO-852DV](#)