

Analog Insulation Tester

✓ **Three Insulation Test Ranges**
With Live Circuit Warning that displays the actual AC voltage measurement

Features:

- Large easy to read analog display
- Three test voltages 250V, 500V, and 1000V
- Insulation Resistance to 400M Ω
- Lock Power On feature for extended test times
- Automatic discharge circuit
- Measures continuity to 3 Ω , Resistance to 500 Ω , and AC Voltage to 600V
- 1.3mA short circuit current
- Complete with heavy duty test leads, alligator clip test lead, 6 x AA batteries, hanging strap, and hard carrying case



Specifications	
Test Voltage	250V/500V/1000V
Insulation Resistance	0 to 100M Ω , 0 to 200M Ω , 0 to 400M Ω
Accuracy	$\pm 5\%$ of scale
AC Voltage	0 to 600V
Accuracy	$\pm 5\%$ of scale
Resistance	1 to 500 Ω
Accuracy	$\pm 3\%$ of scale
Continuity	3 Ω
Accuracy	$\pm 3\%$ of scale
Dimensions	7.9 x 3.6 x 2" (200 x 92 x 50mm)
Weight	1.2lbs (546g) includes batteries

Ordering Information:

380320.....Analog High Voltage Megohmmeter
TL805.....Double Injected Test Leads



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[380320](#)