



WT-40 Dual display pH, mV & TEMP Meter

Keep the costs and risks of maintaining water quality, distribution and waste under control with these easy to use, one touch water management tester. Allows facility managers to take control of monitoring regulatory compliance and troubleshoot corrosion in building water/waste water systems.

- Used to check pH in water testing and treatment applications
- Dual LCD display with pH / mV and temperature (selectable C and F)
- USB port for data download to a PC (cable & software optional)
- Backlight display for use in dark areas
- pH electrode with Automatic Temperature Compensation for measurement accuracy
- 3 points pH calibration with automatic buffer recognition to prevent calibration errors
- Data Hold
- Max/Min and Data Recording
- Low bat indicator
- Auto power off
- Applications include : Pools, Spas, Aquariums, Labs, Aquaculture, Sanitation plants, Car washes, hydroponics, Water & Wastewater treatment and Boilers / Steam generator maintenance

No hassle warranty

No waiting.

No shipping charges.



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)

WT-40 Dual display pH, mV & TEMP Meter

Data Sheet

Specifications

pH Range	0.00~14.00
with High Resolution	0.01pH
pH Accuracy	±0.02pH
mV Range	-199.9 ~ +199.9mV, -1999 ~ +1999mV
mV Resolution	0.1mV(-199.9~+199.9) or 1mV (-1999~+1999)s
mV Accuracy	±0.2mV(-199.9~+199.9) or ±2 mV (-1999~+1999)
Temperature compensation	-5°C to 80°C (23°F to 176°F)
Accuracy	±0.3°C (± 31.5°F to 32.5°F)
Operating Temperature	0°C to 50°C (32°F to 122°F), Max.80%RH
Power Requirements	4x1.5V batteries AAA
Dimension	175 x 70 x 33 mm (6.9 x 2.8 x 1.3 in)
Weight	Approx. 157g (0.35 lb)
Package Contains	Meter, Battery, Instruction manual, Carrying Pouch, Probe, pH Standard Solution

Amprobe® Test Tools

website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
Tel: 877-AMPROBE

Amprobe® Test Tools Europe

In den Engematten 14
79286 Glottertal, Germany
Tel.: +49 (0) 7684 8009 - 0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[WT-40](#)