



### MATERIALS:

BNC: Body – Brass, Tarnish Resistant Plating Center Contact – Gold Plated Beryllium Copper

Insulation – Teflon per ASTM-D-1457

Finish – Body and Fittings – Tarnish resistant, Center Contact – Gold Plated

P.C. Pins – Silver Plated

Marking: “POMONA 4578” located approximately as shown

### RATINGS:

Operating Voltage: 500 VRMS Max.

Operating Temperature: -65°F - +165°C

Nominal Impedance: 50 Ohms

### ORDERING INFORMATION: Model 4578

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

Sales: 8000-490-2361 Fax: 888-403-3360  
Technical Assistance: 800-241-2060

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4578](#)