




# Heyco® Shorty Bushings

Mounting Hole Diameter Range: .187” (4,7 mm) to 1.093” (27,8 mm)

MOUNTING HOLE DIAMETER		PART NO.		DESCRIPTION	PART DIMENSIONS					
in.	mm.	Black	White		A Inside Diameter		B Head Diameter		C Overall Height	
					in.	mm.	in.	mm.	in.	mm.
<b>Single Locking Step for Panel Thickness up to .062” (1,6 mm)</b>										
.187	4,7	2800	2801	B 187-125	.125	3,2	.250	6,4	.237	6,0
.218	5,5	2859	2860	B 218-125	.125	3,2	.281	7,1		
.281	7,1	2853	2854	B 281-218	.218	5,5	.343	8,7		
.312	7,9	2810	2811	B 312-250	.250	6,3	.375	9,5		
.343	8,7	2856	2857	B 343-218	.218	5,5	.406	10,3	.250	6,4
.375	9,5	2803	2804	B 375-250	.250	6,3	.437	11,1		
.406	10,3	2806	2807	B 406-281	.281	7,1	.468	11,9		
.437	11,1	2813	2814	B 437-312	.312	7,9	.500	12,7		
.468	11,9	2817	2818	B 468-343	.343	8,6	.530	13,5		
.500	12,7	2820	2821	B 500-375	.375	9,5	.562	14,3		
.531	13,5	2824	2825	B 531-406	.406	10,3	.593	15,1		
.593	15,1	2833	2834	B 593-468	.468	11,9	.656	16,7		
.625	15,9	2827	2828	B 625-500	.500	12,7	.703	17,9		
.750	19,1	2836	2837	B 750-625	.625	15,9	.828	21,0		
.781	19,8	2844	2845	B 781-625	.625	15,9	.859	21,8		
.875	22,2	2850	2851	B 875-750	.750	19,0	.945	24,0		
1.000	25,4	2847	2848	B 1000-875	.879	22,3	1.060	27,0		
1.093	27,8	2838	2839	B 1093-969	.969	24,6	1.156	29,4	.255	6,5

Standard color black. Consult Heyco for white and other colors.

- For use in panels .062” (1,6 mm) and thinner.
- Lower overall height protrudes less through thin mounting panels; thus Shorty Bushings occupy less “real estate” inside your application.
- Insulating feed-thru bushings for limited internal clearance (minimum .125” or 3,2 mm) applications.
- Insulates and isolates electric or telecommunications cables as well as low RPM shafts and push-pull rods.
- Locking fingers hold securely after only fingertip pressure snap-in installation.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Available in multiple sizes for use in mounting holes from .187” (4,7 mm) to 1.093” (27,8 mm).



SINGLE PANEL DESIGN  
(PANEL MAY BE THINNER)

**Material** Nylon 6/6  
**Certifications** Recognized under the Component Program of Underwriters' Laboratories, File E15331  
 Certified by Canadian Standards Association, File 8919  
**Flammability Rating** 94V-2  
**Material Temperature Index** 257°F (125°C)—Maximum temperature on part not to exceed 221°F (105°C)

Quick  
Specs

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[2800](#) [2803](#) [2824](#) [2820](#) [2827](#) [2850](#) [2810](#) [2836](#) [2838](#) [2806](#) [2844](#) [2853](#) [2817](#) [2813](#)