





## Heyco® Nylon Cable Clamps

- For clamping cable or tubing securely into place.
- Resist corrosion, salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL certification or testing.)
- All parts are size marked in inches and millimeters.
- Molded in black and natural. 94V-0 halogen free nylon available.
- See page 7-18 for Arrow Clips and Push-In Fasteners suitable for securing Heyco Cable Clamps.

MOUNTING HOLE DIAMETER		SCREW SIZE	PART DIMENSION A		PART NO.		DESCRIPTION			
in.	mm.		in.	mm.	Black	Natural				
<b>Light Duty - 3/8" (9,5 mm) Wide, .05" (1,3 mm) Thick</b>										
.170	4,3	8	.125	3,2	<b>3362</b>	<b>3312</b>	CCL 125-170			
			.187	4,7	<b>3363</b>	<b>3313</b>	CCL 187-170			
			.250	6,3	<b>3364</b>	<b>3314</b>	CCL 250-170			
			.312	7,9	<b>3365</b>	<b>3315</b>	CCL 312-170			
			.375	9,5	<b>3366</b>	<b>3316</b>	CCL 375-170			
			.437	11,1	<b>3367</b>	<b>3317</b>	CCL 437-170			
			.500	12,7	<b>3368</b>	<b>3318</b>	CCL 500-170			
.203	5,2	10	.125	3,2	<b>3352</b>	<b>3302</b>	CCL 1/8			
			.187	4,7	<b>3353</b>	<b>3303</b>	CCL 3/16			
			.250	6,3	<b>3354</b>	<b>3304</b>	CCL 1/4			
			.312	7,9	<b>3355</b>	<b>3305</b>	CCL 5/16			
			.375	9,5	<b>3356</b>	<b>3306</b>	CCL 3/8			
			.437	11,1	<b>3357</b>	<b>3307</b>	CCL 7/16			
						.500	12,7	<b>3358</b>	<b>3308</b>	CCL 1/2
			<b>Heavy Duty - 1/2" (12,7 mm) Wide, .06" (1,5 mm) Thick</b>							
.203	5,2	10	.125	3,2	<b>3372</b>	<b>3322</b>	CCH 1/8			
			.187	4,7	<b>3373</b>	<b>3323</b>	CCH 3/16			
			.250	6,3	<b>3374</b>	<b>3324</b>	CCH 1/4			
			.312	7,9	<b>3375</b>	<b>3325</b>	CCH 5/16			
			.375	9,5	<b>3376</b>	<b>3326</b>	CCH 3/8			
			.437	11,1	<b>3377</b>	<b>3327</b>	CCH 7/16			
			.500	12,7	<b>3378</b>	<b>3328</b>	CCH 1/2			
.203	5,2	10	.562	14,3	<b>3379</b>	<b>3329</b>	CCH 9/16			
			.625	15,9	<b>3380</b>	<b>3330</b>	CCH 5/8			
			.687	17,4	<b>3381</b>	<b>3331</b>	CCH 11/16			
			.750	19,1	<b>3382</b>	<b>3332</b>	CCH 3/4			
			.812	20,6	<b>3383</b>	<b>3333</b>	CCH 13/16			
			.875	22,2	<b>3384</b>	<b>3334</b>	CCH 7/8			
						1.000	25,4	<b>3390</b>	<b>3340</b>	CCH 1
			.203	5,2	10	1.125	28,6	<b>3392</b>	<b>3342</b>	CCH 1-1/8
1.187	30,1	<b>3393</b>				<b>3343</b>	CCH 1-3/16			
1.250	31,8	<b>3394</b>				<b>3344</b>	CCH 1-1/4			
1.375	34,9	<b>3396</b>				<b>3346</b>	CCH 1-3/8			
1.500	38,1	<b>3398</b>				<b>3348</b>	CCH 1-1/2			

Standard colors black and natural.



Quick Specs

<b>Material</b>	Nylon 6/6
<b>Certifications</b>	Recognized under the Component Program of Underwriters' Laboratories File E54523
<b>Flammability Rating</b>	94V-2
<b>Material Temperature Index</b>	185°F (85°C) except select cable clamps molded in halogen-free 94V-0 Nylon

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3326](#) [3303](#)