


# CT05 Series Current Sense Transformer



## FEATURES

- Full Selection of Turns Ratios
- Primary Current (Ip) Rated for 25A
- Frequency Range up to 500kHz
- Compact Package



## PACKAGING

- Pcs/Tray: 108
- Trays/Box: 12
- Pcs/Box: 1296


## APPLICATIONS

- DC/DC Converters
- AC/DC Converters


## Mechanical Dimensions in mm



## Footprint



## Schematic



## Electrical Specifications

Part Number	Turns Ratio (Np:Ns)	Sec. Ls <sup>1</sup> (mH, min.)	Sec. DCR (Ω, max.)	ET <sup>5</sup> (V-μS max.)	Hi-Pot
CT05-050	1:50	4.7	0.50	175	4,000
CT05-100	1:100	18.0	2.0	350	4,000
CT05-200	1:200	76.0	4.5	700	4,000
CT05-500	1:500	470	16.0	1750	4,000
CT05-1000	1:1000	1900	50.0	3500	4,000

1. Tested @ 10kHz, 0.1Vrms  
-1000 tested @ 1kHz, 0.1Vrms
2. Electrical specifications at 25°C.
3. Operating temperature range:  
-40°C to +130°C.
4. Meets UL 94V-0.
5. ET rating is based on a bipolar waveform

## Output Voltage and ET Rating Formulas

Rb (Ω): Terminating Resistance  
F (HZ): Freq  
Es (V): Output Voltage  
ET rating is based on a bipolar waveform

$$Es = I_p * R_b / N_s$$

$$ET = Es * 1/2F$$



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## ICE Components:

[CT05-050](#) [CT05-100](#) [CT05-1000](#) [CT05-500](#)