

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0193230006](#)
Status: **Active**
Overview: [Metric Ring Terminals](#)
Description: VersaKrimp Metric Ring Terminal for M3 Stud Size (#5), Un-insulated, Bag

Documents:

[3D Model \(PDF\)](#) [Drawing \(PDF\)](#)
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
Series [19323](#)
Crimp Quality Equipment Yes
Overview [Metric Ring Terminals](#)
Product Name VersaKrimp
Type Ring
UPC 887191289205

Physical

Barrel Type Closed - Brazed
Insulation None
Material - Metal Copper Alloy
Material - Plating Mating Tin
Net Weight 0.546/g
Packaging Type Bag
Stud Size M3
Wire Size AWG N/A
Wire Size mm² 1.00-2.50

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number BB2,5-323-M3

Reference - Drawing Numbers

Sales Drawing SD-19323-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19323 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	640030100
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 01/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19323-0006](#)