



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	MATERIAL	LEGENDS	"A" +/- .062	"B" +/- .062	MARKERS PER CARDS	STD. PKG. QTY.	STD. CTN. CARDS	STYLE
PPM-0 THRU PPM-25	TEDLAR	'0' THRU '25'	.250 (6.35)	1.50 (38.1)	36	25 CARDS	100	A
PPM-1-33	TEDLAR	'1' THRU '33'	.273 (6.93)	1.50 (38.1)	33	25 CARDS	100	B
PPM-A THRU PPM-C	TEDLAR	'A' THRU 'Z'	.250 (6.35)	1.50 (38.1)	36	25 CARDS	100	A

NOTES:
1. MILLIMETER ARE IN ().



CAD FILENAME/LAYERS 100295CD_DC_C10050/04A

PANDUIT CORP. TINLEY PARK, ILLINOIS

PRE-PRINTED MARKER CARDS
PPM TYPE CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .12 (XXX) ± .025
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
RVU

MAT'L:

SCALE
NTS

DATE
09/01/09

SEE TABLE.

DRAWING NO.

C10050

DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
0	9/1/09	RVU		DRAWING RELEASE.	5820	R		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PPM-6](#) [PPM-1](#) [PPM-0](#) [PPM-10](#) [PPM-3](#) [PPM-16](#) [PPM-9](#) [PPM-19](#) [PPM-15](#) [PPM-8](#) [PPM-23](#) [PPM-2](#) [PPM-25](#)
[PPM-7](#) [PPM-4](#) [PPM-5](#) [PPM-24](#) [PPM-11](#) [PPM-13](#) [PPM-18](#) [PPM-17](#) [PPM-1-33](#) [PPM-C](#) [PPM-A](#) [PPM-12](#) [PPM-20](#)
[PPM-B](#) [PPM-14](#)