

Specification for 1W PV Module

(Test condition: 1000W/m², AM1.5, 25°C)

Parameters		Type	1W
		Silicon	Mono-Crystalline Silicon
Maximum Power	Watt		1
Production Tolerance			± 10%
Maximum Power voltage	V		6V
Maximum Power current	A		0.17
Open circuit voltage	V		6.9
Short circuit current	A		0.18
Cells thickness			0.18mm±20µm
size of panel (wide and high)			125*63*3mm
Number of cells			12
Weight per piece (Kgs)			0.12

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Parallax:](#)

[750-00030](#)