






Power Modules

Power Modules Horizontal Versions for Plug-in

With decoupling diodes



RENATA No.	Nominal capacity (mAh)	Nominal voltage (V)	Encapsulated cell	Weight (g)	Maximum dimensions (mm)			
					A	B	C	D
1000-1B	950	3	CR2477N	15.0	30.0	10.0	25.4	22.9

Operating temperature range: -40 °C to +85 °C
 Self-discharge rate: less than 1% per year at 25 °C
 Specifications - module housings: polyamide 66
 - plug-in pins: gold plated

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Renata:](#)

[1000-0B](#) [1000-0](#)