

Schneider Electric USA

1415 South Roselle Road

Palatine, IL 60067

Customer Care Center: 1-888-778-2733

Web: www.schneider-electric.us

Item # ATV312H055M2, Variable Speed Drive



Variable Speed Drive

Variable Speed Drive

SPECIFICATIONS

Family	Altivar 312
Product Line	AC Drives
Output Ampere Rating	3.7
Application	Constant Torque
Enclosure Rating	IP20
Frame Size	4
HP Rating	0.75
kW Rating	0.55
Voltage Rating	208/240VAC
Input Phase	1 Phase
Output Phase	3 Phase
Control Voltage	24Vdc
Logic Input	6
Analog Input	3

Analog Output	1
Logic/Relay Outputs	1 Form C, 1 NO
Weight [lb]	2.31
Weight [kg]	1.05
UL File No.	E116875
CSA File	1464725
Other	CE, GOST, RoHS, NOM, EMITECH
Communication	Modbus and CANopen

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ATV312H055M2](#)